

Garant GRIDLINE

Vario workbench with 2 drawer casings 16G, height 950 mm, Eluplan worktop, dark, 12×20G, Worktop length: 1500/6+7mm



Order data

Order number	922177 1500/6+7
GTIN	4062406118228
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 75; 75; 100; 100; 100; 150; 200

Supplied with:

2 × drawer casings, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer body depth	650 mm
Number of drawers	13
Drawer usable width in G	12
Drawer usable area in G	12×20

Worktop depth	750 mm
Drawer usable depth in G	20
Drawer body height	900 mm
Height	950 mm
Worktop length	1500 mm
Drawer body usable height	800 mm
Drawer usable depth	500 mm
Drawer body width	400 mm
Weight	189 kg
Worktop thickness	50 mm
Drawer usable width	300 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Series	vario
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12x20G
Type of product	Workbench

Accessories

Drawer Drawer front height 200 mm	927500 200
-----------------------------------	------------

Drawer Drawer front height 125 mm	927500 125
Drawer Drawer front height 100 mm	927500 100
Drawer Drawer front height 75 mm	927500 75
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 250 mm	927500 250
Drawer Drawer front height 150 mm	927500 150
Drawer casing 16G with drawers Height / number of drawers 900/7	927300 900/7
Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm	926241 1500
Drawer casing 16G with drawers Height / number of drawers 900/6	927300 900/6