

Garant GRIDLINE

Vario workbench with 2 drawer casings 16G, height 850 mm, Beech marine ply worktop, 12×20G, Worktop length: 1500/6+7mm



Order data

| | |
|--------------|-----------------|
| Order number | 922164 1500/6+7 |
| GTIN | 4062406118143 |
| Item class | 9GG |

Description

Version:

Workbench in sturdy steel construction. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height (left) mm: 75, 75, 100, 100, 150, 200

Drawer front height (right) mm: 75; 75; 75; 75; 100; 100; 200

Supplied with:

2 × drawer casings, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|--------------------------|--------|
| Drawer body depth | 650 mm |
| Drawer usable depth in G | 20 |
| Drawer body height | 800 mm |
| Drawer usable width in G | 12 |

| | |
|---|--|
| Drawer usable width | 300 mm |
| Drawer usable area in G | 12×20 |
| Number of drawers | 13 |
| Drawer body usable height | 700 mm |
| Worktop depth | 750 mm |
| Weight | 183 kg |
| Worktop length | 1500 mm |
| Drawer body width | 400 mm |
| Series | vario |
| Drawer usable depth | 500 mm |
| Worktop thickness | 50 mm |
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg |
| Height | 850 mm |
| Design version | Steel hollow section construction |
| Material thickness | 1 mm |
| Workbench height | 850 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Insert thickness | 50 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 12×20G |
| Type of product | Workbench |

Accessories

| | |
|-----------------------------------|------------|
| Drawer Drawer front height 100 mm | 927500 100 |
|-----------------------------------|------------|

| | |
|--|--------------|
| Lock plate for GridLine Type KO21 | 914227 KO21 |
| Drawer Drawer front height 75 mm | 927500 75 |
| Drawer Drawer front height 150 mm | 927500 150 |
| Drawer Drawer front height 200 mm | 927500 200 |
| Drawer casing 16G with drawers Height / number of drawers 800/6 | 927300 800/6 |
| Drawer casing 16G with drawers Height / number of drawers 800/7 | 927300 800/7 |
| Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm | 926081 1500 |