

Garant GRIDLINE

## Vario workbench with 2 drawer casings 16G, height 850 mm, Eluplan worktop, dark, 12×20G, Worktop length: 1500/6+7mm



### Order data

|              |                 |
|--------------|-----------------|
| Order number | 922167 1500/6+7 |
| GTIN         | 4062406118167   |
| Item class   | 9GG             |

### Description

#### Version:

Workbench in sturdy steel construction. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

#### Fitted with:

Drawer front height (left) mm: 75, 75, 100, 100, 150, 200

Drawer front height (right) mm: 75; 75; 75; 75; 100; 100; 200

#### Supplied with:

2 × drawer casings, worktop.

#### Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

|                           |        |
|---------------------------|--------|
| Worktop thickness         | 50 mm  |
| Drawer usable depth       | 500 mm |
| Drawer usable depth in G  | 20     |
| Drawer body usable height | 700 mm |

|   |  |
|---|--|
| Height  | 850 mm   |
| Drawer body height  | 800 mm   |
| Workbench/desk load capacity - maximum distributed load (on wood) | 1000 kg  |
| Number of drawers   | 13   |
| Drawer body depth   | 650 mm   |
| Drawer body width   | 400 mm   |
| Drawer usable width   | 300 mm   |
| Worktop length  | 1500 mm  |
| Worktop depth   | 750 mm   |
| Series  | vario  |
| Drawer usable area in G   | 12×20  |
| Weight  | 183 kg   |
| Drawer usable width in G  | 12   |
| Design version  | Steel hollow section construction                              |
| Material thickness  | 1 mm   |
| Workbench height  | 850 mm   |
| Drawer/pull-out shelf load capacity                               | 75 kg  |
| Insert thickness  | 50 mm  |
| Drawer runner extension (partial/full extension)                  | 100 %  |
| Cylinder lock   | modular lock barrel  |
| Colour selection  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute  | 12×20G   |
| Type of product   | Workbench  |

## Accessories

|                                   |            |
|-----------------------------------|------------|
| Drawer Drawer front height 200 mm | 927500 200 |
|-----------------------------------|------------|

|   |              |
|---|--------------|
| Drawer Drawer front height 75 mm  | 927500 75    |
| Lock plate for GridLine Type KO21                                       | 914227 KO21  |
| Drawer Drawer front height 150 mm                                       | 927500 150   |
| Drawer Drawer front height 100 mm                                       | 927500 100   |
| Drawer casing 16G with drawers Height / number of drawers 800/7         | 927300 800/7 |
| Drawer casing 16G with drawers Height / number of drawers 800/6         | 927300 800/6 |
| Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm | 926241 1500  |