

Garant GRIDLINE

**Vario workbench, mobile, height 850 mm, Bamboo worktop, 20×20G,
Worktop length mm / number of drawers: 1000/1**


Order data

Order number	923501 1000/1
GTIN	4062406118235
Item class	9GG

Description

NOTE: Colour selection possible
Version:

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport.

Fitted with:

Drawer front height, mm: 125

Supplied with:

2 × support legs with wheels, casing with drawer, storage shelf, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 850 mm

Worktop length: 1000 mm

Worktop depth: 750 mm

Worktop thickness: 50 mm

Drawer body height: 200 mm
 Drawer body width: 600 mm

Technical description

ComfortClose	no
Treadless tyres	yes
Drawer usable depth in G	20
Height	850 mm
Number of drawers	1
Drawer body depth	650 mm
Drawer body width	600 mm
can be lowered	no
Bumper	no
Weight	62.1 kg
Series	vario
Series	vario
Drawer usable width in G	20
Drawer usable depth	500 mm
Material of wheel	Polyurethan
Drawer body usable height	125 mm
Push handle	no
Drawer usable area in G	20×20
Material of worktop	Bamboo
Number of castors with parking brake	2
Worktop thickness	50 mm
Worktop length	1000 mm
Drawer usable width	500 mm
Fixed wheel Ø	125 mm
Worktop depth	750 mm
Castor Ø	125 mm

maximum load capacity, mobile unit	250 kg
Number of fixed wheels without parking brake	2
Drawer body height	200 mm
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Slotted dividers / plain dividers set Drawer front height / type 125/2	950320 125/2
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
Rear panel / storage shelf single-piece suitable for worktop length 700 mm	927140 700

Drawer with one-handed individual drawer release system
Drawer front height 125 mm

927805 125

Slotted dividers / plain dividers set Drawer front height /
type 125/4

950320 125/4