

Garant GRIDLINE

Vario workbench, mobile, height 950 mm, Bamboo worktop, 20×20G, Worktop length mm / number of drawers: 1000/1



Order data

Order number	923511 1000/1
GTIN	4062406118266
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport.

Fitted with:

Drawer front height, mm: 125

Supplied with:

2 × support legs with wheels, casing with drawer, storage shelf, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable width in G	20
--------------------------	----

Castor Ø	125 mm
Drawer body width	600 mm
Number of drawers	1
Bumper	no
Drawer body height	200 mm
Material of wheel	Polyurethan
Material of worktop	Bamboo
Drawer usable depth in G	20
Series	vario
Series	vario
Drawer usable depth	500 mm
Fixed wheel Ø	125 mm
Height	950 mm
Push handle	no
Treadless tyres	yes
ComfortClose	no
Worktop depth	750 mm
Number of castors with parking brake	2
Worktop length	1000 mm
Weight	63.3 kg
Number of fixed wheels without parking brake	2
Drawer body usable height	125 mm
Worktop thickness	50 mm
can be lowered	no
Drawer usable area in G	20×20
maximum load capacity, mobile unit	250 kg
Drawer body depth	650 mm
Drawer usable width	500 mm
Individual drawer release system	One-hand

Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Rear panel / storage shelf single-piece suitable for worktop length 700 mm	927140 700
Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-handed individual drawer release system Drawer front height 125 mm	927805 125