

Garant GRIDLINE

**Vario workbench, mobile, height 850 mm, Eluplan worktop, dark, 20×20G,
Worktop length mm / number of drawers: 1000**



Order data

Order number	923507 1000
GTIN	4062406118310
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Supplied with:

2 × support legs with wheels, 2 × pairs stabilising plates, storage shelf, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Push handle	no
Worktop thickness	50 mm
Worktop depth	750 mm
Weight	40.3 kg
Series	vario

Series	vario
Material of worktop	Eluplan, dark
Number of castors with parking brake	2
Castor Ø	125 mm
Height	850 mm
Number of fixed wheels without parking brake	2
Bumper	no
ComfortClose	no
Fixed wheel Ø	125 mm
Treadless tyres	yes
Number of drawers	0
Material of wheel	Polyurethan
maximum load capacity, mobile unit	250 kg
Worktop length	1000 mm
can be lowered	no
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Rear panel / storage shelf single-piece suitable for worktop length 700 mm

927140 700