

Garant GRIDLINE

**Vario workbench, mobile, height 950 mm, Eluplan worktop, dark, 20×20G,  
Worktop length mm / number of drawers: 1000/1****Order data**

Order number	923517 1000/1
GTIN	4062406118280
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. **Individual drawer release system** prevents the opening of drawers during transport.

**Fitted with:**

Drawer front height, mm: 125

**Supplied with:**

2 × support legs with wheels, casing with drawer, storage shelf, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Number of fixed wheels without parking brake	2
--	---

Weight	58.3 kg
Drawer body height	200 mm
Worktop length	1000 mm
Drawer usable area in G	20×20
Treadless tyres	yes
Material of worktop	Eluplan, dark
Drawer body usable height	125 mm
Drawer usable width in G	20
ComfortClose	no
Worktop depth	750 mm
maximum load capacity, mobile unit	250 kg
Height	950 mm
Push handle	no
Number of castors with parking brake	2
Castor Ø	125 mm
Material of wheel	Polyurethan
Series	vario
Series	vario
Drawer usable depth	500 mm
Number of drawers	1
Worktop thickness	50 mm
Drawer usable width	500 mm
Fixed wheel Ø	125 mm
can be lowered	no
Bumper	no
Drawer body width	600 mm
Drawer usable depth in G	20
Drawer body depth	650 mm
Individual drawer release system	One-hand

Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

## Accessories

Lock plate for GridLine Type KO21	914227 KO21
Rear panel / storage shelfsingle-piece suitable for worktop length 700 mm	927140 700
Drawer with one-handed individual drawer release system Drawer front height 125 mm	927805 125