

Garant GRIDLINE

Vario workbench, mobile, height 950 mm, Beech marine ply worktop, 20×20G, Worktop length mm / number of drawers: 1000



Order data

Order number	923514 1000
GTIN	4062406118334
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Supplied with:

2 × support legs with wheels, 2 × pairs stabilising plates, storage shelf, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Series	vario
Series	vario
Number of castors with parking brake	2
Material of worktop	Beech marine ply

Treadless tyres	yes
Number of fixed wheels without parking brake	2
Number of drawers	0
Material of wheel	Polyurethan
Bumper	no
Height	950 mm
ComfortClose	no
Worktop depth	750 mm
Castor Ø	125 mm
Weight	51.5 kg
can be lowered	no
Push handle	no
maximum load capacity, mobile unit	250 kg
Worktop thickness	50 mm
Surface worktop	clear varnished
Worktop length	1000 mm
Fixed wheel Ø	125 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Rear panel / storage shelf single-piece suitable for worktop length 700 mm

927140 700