

Garant GRIDLINE

## Vario workbench, mobile, height 950 mm, Eluplan worktop, dark, 20×20G, Worktop length mm / number of drawers: 1000



### Order data

Order number	923517 1000
GTIN	4062406118341
Item class	9GG

### Description

#### Version:

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

#### Supplied with:

2 × support legs with wheels, 2 × pairs stabilising plates, storage shelf, worktop.

#### Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

### Technical description

Number of castors with parking brake	2
Treadless tyres	yes
maximum load capacity, mobile unit	250 kg
Number of fixed wheels without parking brake	2

Fixed wheel Ø	125 mm
Number of drawers	0
Bumper	no
Worktop thickness	50 mm
ComfortClose	no
Height	950 mm
can be lowered	no
Castor Ø	125 mm
Material of worktop	Eluplan, dark
Worktop depth	750 mm
Push handle	no
Weight	41.5 kg
Worktop length	1000 mm
Material of wheel	Polyurethan
Series	vario
Series	vario
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

---

## Accessories

Rear panel / storage shelf single-piece suitable for worktop length 700 mm

---

927140 700