

Garant GRIDLINE

**Vario workbench, mobile, height 950 mm, Bamboo worktop, 20×20G,
Worktop length mm / number of drawers: 1000****Order data**

Order number	923511 1000
GTIN	4062406118327
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with storage shelf depth 300 mm. With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Supplied with:

2 × support legs with wheels, 2 × pairs stabilising plates, storage shelf, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Height	950 mm
Castor Ø	125 mm
Series	vario
Series	vario

maximum load capacity, mobile unit	250 kg
ComfortClose	no
Weight	46.5 kg
Worktop depth	750 mm
Treadless tyres	yes
Number of fixed wheels without parking brake	2
Bumper	no
Material of worktop	Bamboo
Push handle	no
Number of castors with parking brake	2
Number of drawers	0
Fixed wheel Ø	125 mm
can be lowered	no
Material of wheel	Polyurethan
Worktop thickness	50 mm
Worktop length	1000 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Rear panel / storage shelf single-piece suitable for worktop length 700 mm

927140 700