

Garant GRIDLINE

**Vario workbench with drawer casing 24G, height 850 mm, Bamboo worktop, 20×20G, Worktop length: 2000/2mm****Order data**

Order number	922581 2000/2
GTIN	4062406214548
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75#150

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Drawer usable depth in G	20

Worktop length	2000 mm
Drawer body width	600 mm
Worktop depth	750 mm
Worktop thickness	50 mm
Drawer usable area in G	20×20
Drawer body height	300 mm
Drawer body depth	650 mm
Drawer body usable height	225 mm
Height	850 mm
Number of drawers	2
Drawer usable depth	500 mm
Series	vario
Drawer usable width in G	20
Weight	126 kg
Drawer usable width	500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

File set Number of tools 6	952253 6
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Mat for drawers Dimension in G 20X20	951830 20X20
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Screwdriver set Number of tools 10	953521 10
Overlay of plasticised PVC transparent Width 2000 mm	951951 2000
Drawer Drawer front height 150 mm	927800 150
Pliers set Number of tools 5	954305 5
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Cleaner and care oil set Type 1	926403 1
Lock plate for GridLine Type KO21	914227 KO21
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Drawer Drawer front height 75 mm	927800 75
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Stabilising plate Type 1	927122 1
Support leg Height 800 mm	927000 800
	926001 2000

Worktop thickness 50 mm of bamboo strips glued cross-wise  
Worktop length 2000 mm

Drawer casing 24G with drawers Height / number of  
drawers 300/2

927600 300/2