

Garant GRIDLINE

**Vario workbench with drawer casing 24G, height 950 mm, Eluplan worktop, dark, 20×20G, Worktop length: 2000/2mm****Order data**

Order number	922597 2000/2
GTIN	4062406214692
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75#150

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Drawer body height	300 mm
Worktop length	2000 mm

Weight	127 kg
Drawer usable width	500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Worktop depth	750 mm
Number of drawers	2
Series	vario
Drawer body usable height	225 mm
Drawer usable depth in G	20
Drawer usable depth	500 mm
Drawer usable width in G	20
Worktop thickness	50 mm
Height	950 mm
Drawer usable area in G	20×20
Drawer body width	600 mm
Drawer body depth	650 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 75 mm	927800 75
Stabilising plate Type 1	927122 1
Worktopwith dark grey plastic coating (Eluplan) Worktop length 2000 mm	926241 2000
Support leg Height 900 mm	927000 900
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2