

bimos

**Sitting-standing stool – ESD, PU foam, with glides, Type: ESD****Order data**

Order number	972701 ESD
GTIN	4016849562834
Item class	96B

**Description****Version:**

**5-star aluminium base** (Ø 600 mm). Continuous height adjustment by **gas pressure spring**. Seat of SoftTouch PU foam with ribbed profile. **Soft seat with non-slip surface**, ribbed profile allows air circulation (climate comfort). **Ergonomic backrest** (height 190mm) supports correct posture. PU foam, soft, comfortable, washable.

**Application:**

Ideal combination of standing and sitting. For use at sitting or standing workstations, or a combination of both.

Sitting-standing stool with glides – for a working height of 720 – 1000 mm.

**Standard:**

**Leitfähig nach DIN 61340-5-1.**

**DIN 68877**

**Technical description**

Seat width	340 mm
Type of height adjustment	Height adjustment lever

Standard	DIN 68877
Colour of seat material	black
Height adjustment version	Gas pressure spring
Backrest height	190 mm
Support frame version	5-point star base
Seat tilt adjustment	no
Material of base	Polished aluminium
Seat depth	300 mm
Base version	Glides
Star base Ø	580 mm
Material of seat surface	PU foam
with backrest	yes
Load capacity chair	120 kg
electrostatic characteristic	EGB/ESD
Height adjustment range	510 - 780 mm
Type of product	ESD standing stool

---

## Accessories

ESD glides(1 set = 5 pieces)	963190
------------------------------	--------