

Garant GRIDLINE

Mobile base for Ready-to-go workbenches, Type: 1200



Order data

| | |
|--------------|---------------|
| Order number | 927271 1200 |
| GTIN | 4062406118600 |
| Item class | 9GG |

Description

Version:

Base frame is fitted with 2 castors and 2 fixed wheels \varnothing 100 mm with grey treadless solid rubber tyres. Undercarriage load capacity up to **400 kg** (workbench incl. contents). 2-component Haptoprene® handle on a raise-lower device.

Suitable for:

Ready-to-go workbenches with casing widths 1200 mm in total and sub-frame width 1300 mm. No. 927241 size 1200/2, 1200/3; No. 927261 size 1200/2, 1200/3.

Colour:

Anthracite RAL 7016 **powder coated, not configurable.**

Note:

Wheels and push handle unsuitable for retrofitting. Workbenches with wheels and push handle must be equipped with a one-hand individual drawer release system. Unsuitable for workbenches with recessed open casings.

Design version: Steel hollow section construction

Height: 200 mm

Width: 1200 mm

Depth: 700 mm

maximum load capacity, mobile unit: 400 kg

Technical description

| | |
|------------------------------------|---------|
| Width | 1200 mm |
| maximum load capacity, mobile unit | 400 kg |

| | |
|--------------------|-----------------------------------|
| Depth | 700 mm |
| Height | 200 mm |
| Series | Ready-to-go |
| Series | Ready-to-go |
| Design version | Steel hollow section construction |
| Material thickness | 1 mm |
| Type of product | Wheels and push handle |