

Garant GRIDLINE

Mobile base for Ready-to-go workbenches, Type: 1000**Order data**

Order number	927271 1000
GTIN	4062406118594
Item class	9GG

Description**Version:**

Base frame is fitted with 2 castors and 2 fixed wheels Ø 100 mm with grey treadless solid rubber tyres. Undercarriage load capacity up to **400 kg** (workbench incl. contents). 2-component Haptoprene® handle on a raise-lower device.

Suitable for:

Ready-to-go workbenches with casing widths 1000 mm in total and sub-frame width 1100 mm. No. 927241 size 1000, No. 927261 size 1000.

Colour:

Anthracite RAL 7016 **powder coated, not configurable.**

Note:

Wheels and push handle unsuitable for retrofitting. Workbenches with wheels and push handle must be equipped with a one-hand individual drawer release system. Unsuitable for workbenches with recessed open casings.

Technical description

maximum load capacity, mobile unit	400 kg
Height	200 mm
Series	Ready-to-go
Series	Ready-to-go
Depth	700 mm

Width	1030 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Type of product	Wheels and push handle