

**HOLEX perforated rear panel, Height 962 mm, suitable for type: 2000****Order data**

Order number	929651 2000
GTIN	4062406118686
Item class	92W

Description**Version:**

Stand of sheet metal 40×40 mm for screwing to the worktop. Perforated sheet metal panel between the columns.

Colour:

RAL 7035 light grey **powder coated**.

Note:

Articles in the support column attachment range cannot be inserted into the perforated panel.

Technical description

Depth	25 mm
Height	962 mm
suitable for type	2000 mm
Perforated panel version	single-sided
Width	1920 mm
Design version	Steel hollow section construction

Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Product name attribute	Height 962 mm
Type of product	Perforated rear panel