



## Pneumatic scriber DynaPen®, Type: 10850



### Order data

Order number	079708 10850
GTIN	616026108509
Item class	03R

### Description

#### Version:

DynaPen pencil-sized pneumatic pen with **accessories set (collet 1/8 inch)**. The pulsating drive movement (amplitude 0.018 mm) permits **many applications** such as engraving, lettering, light cleaning, and filing work, as well as deburring etc.

#### Supplied with:

1.4 m connection hose, 3 files, engraving tip, and a hexagon key.

#### Note:

See No. 529420 for suitable diamond mini-files.

maximum air consumption: 28.2 l/min

Impact frequency: 233 Hz

Connection thread: NPT

Compressed air connection: 1/4 inch

Weight: 0.26 kg

Operating noise: 79 dB(A)

### Technical description

Weight	0.26 kg
Ø	23 mm
Manufacturer's designation	10850
Impact frequency	233 Hz
maximum air consumption	28.2 l/min

maximum vibration to EN	8 m/s <sup>2</sup>
Operating noise	79 dB(A)
Length	108 mm
Compressed air connection	1/4 inch
Connection thread	NPT
Type of product	Scriber

---

## Accessories

Diamond mini-file Grit D126 (medium) general-purpose Type 1	529420 1
Diamond mini-file Grit D126 (medium) general-purpose Type 1K	529420 1K
Diamond mini-file Grit D126 (medium) general-purpose Type 4	529420 4