

Garant GRIDLINE

Janitor's cabinet with Plain sheet metal swing doors, width mm / Model: 750/K



Order data

Order number	987001 750/K
GTIN	4062406118822
Item class	9GI

Description

Version:

Universal cabinet for storing cleaning materials, cleaning devices and clothing. Mountings for galvanised shelves at 25-mm intervals.

Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor. Shelf load capacity 25 kg. Holes in partition housing can be used **for attaching Easyfix hooks and holders** (in Group 95).

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

The janitor's cabinets are dimensionally compatible with the GridLine cabinets of 20G in depth and can be combined with them as required.

Further accessories such as shelves and drawers can be found in Group 94.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 750 mm

Depth: 500 mm

Usable height: 1840 mm

Number of hooks: 3

Weight: 78 kg

Technical description

Number of hooks	3
Height	2000 mm
Depth	500 mm
Weight	78 kg
Width	750 mm
Model	K
Cabinet fronts	Plain sheet metal swing doors
Usable height	1840 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Janitor's cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------