

Garant**Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone, Cross-head size / overall length: 1/25mm****Order data**

Order number	675115 1/25
GTIN	4062406118105
Item class	61F

Description**Version:**

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

With torsion zone, **toughened**. The torsion zone absorbs the peaks of force when screw driving. This protects the screw profile and achieves longer tool life (apart from size TX40).

Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

Standard:

DIN ISO 1173.

Material:

Chrome vanadium special alloy, **high strength**.

Technical description

Cross-head size	1
overall length	25 mm
Bit hexagon shank	C 6,3
Standard	DIN ISO 1173
Drive profile	Pozidriv screwdriver
Type of product	Bit tool

