



## Mini burr Z7 – medium, diamond cut, Carbide, Type: H0307



### Order data

Order number	546910 H0307
GTIN	4045197724328
Item class	52D

### Description

#### Version:

**HOLEX** – burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm.

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Toothing grit designation	medium
Type of cut	staggered teeth
Overall length	38 mm
Shape description	Flame
Tooth type abbreviation	Z7
Shape	H0307
Head $\varnothing$	3 mm
Shank $\varnothing$	3 mm
Head length	6 mm
Series	#Tooth configuration Z7
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		