

Garant
Clamp toolholder, left-hand, Shank / insert size: 40/19mm

Order data

Order number	250017 40/19
GTIN	4062406119126
Item class	21T

Technical description

Overall length L	250 mm
Shim	259031 18
Clamp, screw, spring	259035 1
ISO code toolholder	DCLNR/L 4040S19
Functional width L ₄	50 mm
suitable indexable insert	CN.. 1906..
Insert size	19 mm
Head length L ₁	45 mm
Series	QuickTurn
Shank size	40 mm
Shim screw	259025 13
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw 10 pieces Type 2	259026 2
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2
Shim Type 36	259031 36
Shim Type 18	259031 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500