

Garant**Lever lock toolholder, left-hand, Shank / insert size: 40/19mm****Order data**

Order number	250019 40/19
GTIN	4062406119225
Item class	21T

Technical description

Insert size	19 mm
Shim pins pack	259044 1
Functional width L ₄	50 mm
suitable indexable insert	CN.. 1906..
Shim	259031 17
Shim punches pack	259047 1
ISO code toolholder	PCLNR/L 4040S19
Lever screw	259018 1
Lever	259015 1
Overall length L	250 mm
Head length L ₁	45 mm
Series	QuickTurn
Shank size	40 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 16	259031 16
Lever Type 13	259015 13
Lever Type 1	259015 1
Shim punches set 10 pieces Type 1	259047 1
Lever screw Type 13	259018 13
Set of shim pins 10 pieces Type 7	259044 7
Shim Type 36	259031 36
Set of shim pins 10 pieces Type 1	259044 1
Lever screw Type 1	259018 1