

**Garant**
**Lever lock toolholder, left-hand, Shank / insert size: 40/19mm**

**Order data**

Order number	250021 40/19
GTIN	4062406119249
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	35 mm
Shank size	40 mm
Lever	259015 1
Lever screw	259018 1
Shim pins pack	259044 1
Head length L <sub>1</sub>	48 mm
suitable indexable insert	CN.. 1906..
ISO code toolholder	PCBNR/L 4040S19
Overall length L	250 mm
Shim punches pack	259047 1
Series	QuickTurn
Shim	259031 17
Insert size	19 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 16	259031 16
Shim punches set 10 pieces Type 1	259047 1
Shim Type 36	259031 36
Lever screw Type 13	259018 13
Lever Type 1	259015 1
Set of shim pins 10 pieces Type 1	259044 1
Set of shim pins 10 pieces Type 7	259044 7
Lever screw Type 1	259018 1
Lever Type 13	259015 13