

Garant
Lever lock toolholder, right-hand, Shank / insert size: 40/19mm

Order data

Order number	250022 40/19
GTIN	4062406119256
Item class	21T

Technical description

suitable indexable insert	CN.. 1906..
ISO code toolholder	PCKNR/L 4040S19
Head length L ₁	45 mm
Shim punches pack	259047 1
Shim	259031 17
Lever	259015 1
Overall length L	250 mm
Insert size	19 mm
Series	QuickTurn
Shim pins pack	259044 1
Shank size	40 mm
Functional width L ₄	50 mm
Lever screw	259018 1
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 7	259044 7
Shim Type 36	259031 36
Lever screw Type 13	259018 13
Shim punches set 10 pieces Type 1	259047 1
Set of shim pins 10 pieces Type 1	259044 1
Shim Type 16	259031 16
Lever screw Type 1	259018 1
Lever Type 13	259015 13
Lever Type 1	259015 1