

**ALLURIS**
**FMI-B20 Digital peak force gauge, Measuring range: 2500N**

**Order data**

Order number	478983 2500
GTIN	4260244680857
Item class	47F

**Description**
**Version:**

- **Sturdy force gauges in a handy aluminium die-cast housing for compressive and tensile forces from 0.001 to 2500 N.**
- **Overload protection up to 500% and protected measurement shaft.**
- **Attachment thread for additional handles.**
- **Precise positioning in test stands by a guide pin.**
- **High measurement rate for precise recording of peak values to determine fracture or tearing forces.**

**Advantage:**

Operating time up to 150 h without mains power thanks to the rechargeable LiPo battery.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

**Measurement of compressive and tensile forces in quality assessment and production.** For use as a mobile manual measurement gauge both in outdoor areas and in test stands or jigs. Attachment thread integrated into the housing permit attachment in test stands or mounting of additional handles.

**Supplied with:**

Force gauge in a protective case. Screw-on accessories for force transfer (flat head, slot head, cone, hook). Quick-start instructions.

## Technical description

Height	29 mm
Width	82 mm
Connection thread	M10
Measuring range	2500 N
Resolution	1 N
IP Index of Protection	IP 65
Length	150 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Measurement technology	digital
Calibration	Price on request
Type of product	Draw bar pulling force gauge