

Garant GRIDLINE

Workstation mLevel with pale Eterlux worktop, Length: 1500mm



Order data

Order number	920004 1500
GTIN	4062406119430
Item class	91P

Description

Version:

Workstation mLevel, the workstation that adapts to your needs. Classic manual height adjustment in 25-mm steps using a support leg with securing bolts by which the height of the entire workstation is adjusted. Scaling on the inside of the table showing the exact working height for ease of operation.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Technical description

Width	1500 mm
Model	mLevel
Weight	70 kg
Worktop covering	Eterlux (melamine / phenolic resin)
Depth	800 mm
Control panel with display and memory functions	no
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Worktop depth	700 mm

Stepless height adjustment	no
Series	Workstation
Coating thickness	2.7 mm
Worktop length	1500 mm
Principle of height adjustment	complete structure
Material of worktop	Eterlux
Surface worktop	Coating very scratch-resistant and heat-resistant
Worktop thickness	40 mm
Colour of worktop surface	pale grey
Height adjustment workstation	750-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Shelf 810 mm usable depth suitable for type 1500	920211 1500
Pair of roller tracks Type 1	920212 1
Kanban base frame formLevel and eLevel+ Depth 400 mm	920201 400
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5
Support columns Height 962 mm	928010 962
Support columns Height 200 mm	928010 200

16G computer casing Height 500 mm	927335 500
Drawer casing, 16G mobile Casing height mm / number of drawers 500/5	927315 500/5
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Drawer casing 24G with drawers Height / number of drawers 400/4	927600 400/4
Multifix suitable for type 300	928201 300
Keyboard drawer Type 1	927341 1
Support columns Height 481 mm	928010 481
Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm	927620 500/5
Support columns Height 1362 mm	928010 1362
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Drawer casing, 16G mobile Casing height mm / number of drawers 500/4	927315 500/4
Drawer casing, 16G mobile Casing height mm / number of drawers 500/3	927315 500/3
PC holder Type M	928753 M
Drawer casing 16G with drawers Height / number of drawers 300/3	927300 300/3
Drawer casing 16G with drawers Height / number of drawers 400/4	927300 400/4
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3
Drawer casing, 16G mobile Casing height mm / number of drawers 400/4	927315 400/4
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2