

Garant GRIDLINE

mLevel workstation with dark grey Eluplan worktop, Length: 2000mm**Order data**

Order number	920002 2000
GTIN	4062406119416
Item class	91P

Description**Version:**

Workstation mLevel, the workstation that adapts to your needs. Classic manual height adjustment in 25-mm steps using a support leg with securing bolts by which the height of the entire workstation is adjusted. Scaling on the inside of the table showing the exact working height for ease of operation.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Technical description

Stepless height adjustment	no
Width	2000 mm
Worktop depth	700 mm
Worktop length	2000 mm
Weight	80 kg
Material of worktop	Eluplan
Worktop covering	Eluplan (plastic), (linoleum covering)
Depth	800 mm

Principle of height adjustment	complete structure
Surface worktop	Coating anti-static, highly abrasion-resistant, medium hardness, not colour-fast
Colour of worktop surface	dark grey
Worktop thickness	40 mm
Model	mLevel
Series	Workstation
Control panel with display and memory functions	no
Coating thickness	2 mm
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Height adjustment workstation	750-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Support columns Height 962 mm	928010 962
Support columns Height 481 mm	928010 481
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3
Drawer casing, 16G mobile Casing height mm / number of drawers 400/4	927315 400/4
Multifix suitable for type 300	928201 300

PC holder Type M	928753 M
Keyboard drawer Type 1	927341 1
Drawer casing 24G with drawers Height / number of drawers 400/4	927600 400/4
Drawer casing 16G with drawers Height / number of drawers 300/3	927300 300/3
Drawer casing, 16G mobile Casing height mm / number of drawers 500/5	927315 500/5
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2
Support columns Height 1362 mm	928010 1362
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Drawer casing 16G with drawers Height / number of drawers 400/4	927300 400/4
16G computer casing Height 500 mm	927335 500
Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm	927620 500/5
Drawer casing, 16G mobile Casing height mm / number of drawers 500/3	927315 500/3
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2
Drawer casing, 16G mobile Casing height mm / number of drawers 500/4	927315 500/4
Support columns Height 200 mm	928010 200