

Garant GRIDLINE

Workstation mLevel with pale Eterlux worktop, Length: 2000mm



Order data

| | |
|--------------|---------------|
| Order number | 920004 2000 |
| GTIN | 4062406119447 |
| Item class | 91P |

Description

Version:

Workstation mLevel, the workstation that adapts to your needs. Classic manual height adjustment in 25-mm steps using a support leg with securing bolts by which the height of the entire workstation is adjusted. Scaling on the inside of the table showing the exact working height for ease of operation.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Technical description

| | |
|---|-------------------------------------|
| Worktop depth | 700 mm |
| Model | mLevel |
| Principle of height adjustment | complete structure |
| Worktop covering | Eterlux (melamine / phenolic resin) |
| Colour of worktop surface | pale grey |
| Control panel with display and memory functions | no |
| Weight | 80 kg |
| Stepless height adjustment | no |

| | |
|---|--|
| Worktop length | 2000 mm |
| Coating thickness | 2.7 mm |
| Series | Workstation |
| Material of worktop | Eterlux |
| Width | 2000 mm |
| Depth | 800 mm |
| Surface worktop | Coating very scratch-resistant and heat-resistant |
| Height adjustment range (worktop surface) from – to | 750 - 1000 mm |
| Worktop thickness | 40 mm |
| Height adjustment workstation | 750-1000 mm |
| Design version | Steel hollow section construction |
| Workbench/desk load capacity - maximum distributed load (on wood) | 250 kg |
| Type of height adjustment | mechanical |
| Insert thickness | 40 mm |
| Height adjustment | 25 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Work table |

Accessories

| | |
|--|--------------|
| Drawer casing 16G with drawers Height / number of drawers 300/3 | 927300 300/3 |
| PC holder Type M | 928753 M |
| Keyboard drawer Type 1 | 927341 1 |
| Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm | 927620 500/5 |
| Drawer casing 24G with drawers Height / number of drawers 300/3 | 927600 300/3 |

| | |
|--|--------------|
| Support columns Height 962 mm | 928010 962 |
| Support columns Height 481 mm | 928010 481 |
| Support columns Height 1362 mm | 928010 1362 |
| Drawer casing 16G with drawers Height / number of drawers 400/3 | 927300 400/3 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/4 | 927315 500/4 |
| Drawer casing 16G with drawers Height / number of drawers 300/2 | 927300 300/2 |
| Drawer casing 24G with drawers Height / number of drawers 500/5 | 927600 500/5 |
| Drawer casing 24G with drawers Height / number of drawers 200/1 | 927600 200/1 |
| Multifix suitable for type 300 | 928201 300 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/5 | 927315 500/5 |
| Support columns Height 200 mm | 928010 200 |
| Drawer casing 24G with drawers Height / number of drawers 300/2 | 927600 300/2 |
| Drawer casing 16G with drawers Height / number of drawers 400/4 | 927300 400/4 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 400/4 | 927315 400/4 |
| Drawer casing 24G with drawers Height / number of drawers 400/4 | 927600 400/4 |
| 16G computer casing Height 500 mm | 927335 500 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/3 | 927315 500/3 |