

Garant GRIDLINE

Workstation mLevel with pale Eterlux worktop, Length: 1000mm



Order data

Order number	920004 1000
GTIN	4062406119423
Item class	91P

Description

Version:

Workstation mLevel, the workstation that adapts to your needs. Classic manual height adjustment in 25-mm steps using a support leg with securing bolts by which the height of the entire workstation is adjusted. Scaling on the inside of the table showing the exact working height for ease of operation.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Technical description

Coating thickness	2.7 mm
Principle of height adjustment	complete structure
Colour of worktop surface	pale grey
Surface worktop	Coating very scratch-resistant and heat-resistant
Series	Workstation
Material of worktop	Eterlux
Worktop thickness	40 mm

Worktop length	1000 mm
Stepless height adjustment	no
Control panel with display and memory functions	no
Weight	60 kg
Width	1000 mm
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Worktop depth	700 mm
Worktop covering	Eterlux (melamine / phenolic resin)
Model	mLevel
Depth	800 mm
Height adjustment workstation	750-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Kanban base frame formLevel and eLevel+ Depth 400 mm	920201 400
Pair of roller tracks Type 1	920212 1
Shelf 810 mm usable depth suitable for type 1000	920211 1000
Multifix suitable for type 300	928201 300
Support columns Height 962 mm	928010 962
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3

PC holder Type M	928753 M
Drawer casing 16G with drawers Height / number of drawers 400/4	927300 400/4
Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm	927620 500/5
Support columns Height 200 mm	928010 200
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
16G computer casing Height 500 mm	927335 500
Keyboard drawer Type 1	927341 1
Drawer casing 24G with drawers Height / number of drawers 300/2	927600 300/2
Support columns Height 481 mm	928010 481
Drawer casing, 16G mobile Casing height mm / number of drawers 400/4	927315 400/4
Support columns Height 1362 mm	928010 1362
Drawer casing, 16G mobile Casing height mm / number of drawers 500/5	927315 500/5
Drawer casing, 16G mobile Casing height mm / number of drawers 500/3	927315 500/3
Drawer casing 16G with drawers Height / number of drawers 300/3	927300 300/3
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Drawer casing 24G with drawers Height / number of drawers 400/4	927600 400/4
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2
Drawer casing, 16G mobile Casing height mm / number of drawers 500/4	927315 500/4
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5