

Garant GRIDLINE

Corner workstation with base frame with Eterlux worktop, light, Worktop length: 1000mm



Order data

Order number	920102 1000
GTIN	4062406119584
Item class	91P

Description

Version:

Corner workstation for workstation. Height adjustment in 25-mm steps using a support leg with securing bolts. With base frame of sheet metal and square hollow section, load capacity **250 kg**.

Suitable for:

Workstation mLevel, eLevel, eLevel+. No electric height adjustment of the corner workstation possible.

Colour:

Support leg RAL 7016 anthracite (not configurable), **side and back panels** RAL 7035 light grey, **powder-coated**.

Note:

If a corner workstation is combined with eLevel or eLevel+ workstation, side plates at the workstation are a mandatory requirement.

Technical description

Colour of worktop surface	pale grey
Depth	800 mm
Width	1100 mm
Worktop length	1000 mm

Data sheet

Coating thickness	2.7 mm
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Worktop thickness	40 mm
Worktop covering	Eterlux (melamine / phenolic resin)
Surface worktop	Coating very scratch-resistant and heat-resistant
Control panel with display and memory functions	no
Tapering to worktop depth	700 mm
Stepless height adjustment	no
Material of worktop	Strip wood core with Eterlux covering
Weight	80 kg
Worktop depth	1000 mm
Principle of height adjustment	complete structure
Series	Workstation
Design version	Steel hollow section construction
Height adjustment workstation	750-1000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Corner workstation