

Garant GRIDLINE

**Corner workstation with base frame with dark grey Eluplan worktop,
Worktop length: 1000mm****Order data**

Order number	920101 1000
GTIN	4062406119577
Item class	91P

Description**Version:**

Corner workstation for workstation. Height adjustment in 25-mm steps using a support leg with securing bolts. With base frame of sheet metal and square hollow section, load capacity **250 kg**.

Suitable for:

Workstation mLevel, eLevel, eLevel+. No electric height adjustment of the corner workstation possible.

Colour:

Support leg RAL 7016 anthracite (not configurable), **side and back panels** RAL 7035 light grey, **powder-coated**.

Note:

If a corner workstation is combined with eLevel or eLevel+ workstation, side plates at the workstation are a mandatory requirement.

Technical description

Worktop thickness	40 mm
Colour of worktop surface	dark grey
Weight	80 kg
Depth	800 mm

Series	Workstation
Coating thickness	2 mm
Principle of height adjustment	complete structure
Control panel with display and memory functions	no
Tapering to worktop depth	700 mm
Material of worktop	Strip wood core with Eluplan plastic covering
Stepless height adjustment	no
Surface worktop	Coating anti-static, highly abrasion-resistant, medium hardness, not colour-fast
Width	1100 mm
Height adjustment range (worktop surface) from – to	750 - 1000 mm
Worktop length	1000 mm
Worktop covering	Eluplan (plastic), (linoleum covering)
Worktop depth	1000 mm
Design version	Steel hollow section construction
Height adjustment workstation	750-1000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Corner workstation