

**Instant adhesive, 20 g, Type: FAST****Order data**

Order number	083361 FAST
GTIN	4062406120337
Item class	02A

**Description****Version:**

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity. Quick-curing, low viscosity, suitable for **EPDM elastomers, solid rubber, foam rubber and plastic**. Perfect for the production of O-rings

**Note:**

Not available in all countries. Express delivery not available.

**Technical description**

Labelling of hazardous substances	GHS07: Exclamation mark
Tensile shear strength	10 - 20 N/mm <sup>2</sup>
Touch dry after	10 - 30 s
Dynamic viscosity	10 - 20 mPas
Storage temperature	20 °C
Colour	transparent

Operating temperature range	-55 - 95 °C
Working life after date of manufacture	12 mo
Shape	liquid
Tensile strength	10 - 20 N/mm <sup>2</sup>
Chemical basis	Ethyl cyanoacrylate
Density	1.06 g/cm <sup>3</sup>
Suitable for material	Elastomer
Suitable for material	Rubber
Suitable for material	Plastic
Capacity	20 ml
Product name attribute	20 g
Type of product	Instant adhesive