



Adhesive, 50 ml, Manufacturer ID: 82-33



Order data

Order number	083345 82-33
GTIN	8029822064054
Item class	08G

Description

Version:

When using joining as a production technique, two or more components are connected through positive contact. When using the adhesive, the full jointing face is used to establish a solid connection. It allows for high force transfer and dynamic loads (high shear strength).

Application:

High-strength, for small gaps, even where some slight oily contamination is present. Ideal for securing bearings.

Note:

Surfaces should first be treated with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Manufacturer's designation	82-33
Labelling of hazardous substances	GHS05: Corrosive
Labelling of hazardous substances	GHS07 caution
Touch dry after	5 - 10 min
for thread size M to	M12

Suitable for application area	Bearing attachment
Suitable for application area	Joint connection
Suitable for application area	oily surfaces
Chemical basis	anaerobic methacrylate
Colour	green
Storage temperature	25 °C
Dynamic viscosity	120 - 180 mPas
Capacity	50 ml
for thread types	All
Shape	liquid
minimum break-away torque	20 Nm
Maximum gap size	0.1 mm
Suitable for material	Metal
Characteristics	thixotropic
Characteristics	vibration-resistant
Characteristics	resistant to thermal shocks
Working life after date of manufacture	12 mo
Operating temperature range	-55 - 150 °C
Flashpoint	100 °C
Functional strength to	1 - 3 h
Strength class	high-strength
Density	1.1 g/cm ³
Product name attribute	50 ml
Type of product	Jointing product

Accessories

Cleaner and degreaser spray Manufacturer's product number 7061

083391 7061

Cleaner and degreaser spray Manufacturer's product
number 7063

083392 7063