



Safety helmet EuroGuard, Colour: BLUE



Order data

Order number	097802 BLUE
GTIN	4017765057480
Item class	09K

Description

Version:

Light-weight safety helmet of High-Density Polyethylene with **increased lateral stiffness** thanks to double wall internal profile. Ideally suited to working outdoors and at low **temperatures down to -20 °C**. The **large front face** provides an area 5 x 5 cm for printing graphics. With **adjustable lateral ventilation**.

- **6-point strap attachment, height adjustable**
- **30 mm Euro slot mounting**
- **Ecological leather sweatband**
- **Straight shape with rain channel**
- **With rotary catch**

Application:

Building trade, building and civil engineering.

Standard:

DIN EN 397

Suitable for:

Ear defenders No. 097753; 097756.

Material of helmet shell: HDPE

Width adjustment: Rotary catch

Size: 53 - 61 cm

Weight: 340 g

Technical description

Width adjustment	Rotary catch
Colour	BLUE
Weight	340 g
Resistance to cold	Down to -20 °C
Size	53 - 61 cm
Material of helmet shell	HDPE
Type of product	Safety helmet

Accessories

Ear defenders Peltor™ Optime™ helmet series Type 2	097753 2
Ear defenders Peltor™ Optime™ helmet series Type 3	097753 3
Ear defenders Type HELMET	097795 HELMET
Ear defenders Peltor™ Optime™ helmet series Type 1	097753 1