



## Cordless hammer drill, Type: M18CHX



### Order data

Order number	075530 M18CHX
GTIN	4002395160594
Item class	03L

### Description

#### Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**
- **FIXTEC tool quick-change system for switching between the SDS-Plus chuck and the quick-release metal drill chuck, without using tools.**
- **Zero rotation for easy chisel work.**
- **Safety clutch protects user and machine if the drill jams.**
- **AVS anti-vibration system.**

**18 V / 5.0 Ah Li-ion cordless hammer drill** with brushless POWERSTATE™ EC motor, optimised for drilling in concrete and masonry. Redlink Plus™ electronics – overload protection for long working life of the battery, motor and gearbox.

For drilling in concrete up to Ø 26 mm.

#### Advantage:

Anti-vibration system.

#### Supplied with:

Supplied with FIXTEC SDS-plus adapter, quick-change chuck 1.5 – 13 mm, additional handle with depth stop, quick charger, 2 × 18V batteries, carrying case

#### Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Shank: SDS Plus

Manufacturer's designation: M18CHX-502X

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 A·h

Battery voltage: 18 V

Speed range: 0 - 1400 min<sup>-1</sup>

maximum twist drill size Ø in steel: 13 mm

## Technical description

Tool arbor shape	SDS-Plus
maximum hammer rate	4900 min <sup>-1</sup>
maximum twist drill size Ø in concrete	26 mm
maximum vibration to EN	8.9 m/s <sup>2</sup>
Battery voltage	18 V
Impact energy	2.5 J
Manufacturer's designation	M18CHX-502X
Weight	3.5 kg
Battery capacity	5 A·h
maximum twist drill size Ø in wood	30 mm
maximum twist drill size Ø in steel	13 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Packaging	Modular case (HD=Heavy Duty)
Speed range	0 - 1400 min <sup>-1</sup>
Shank	SDS Plus
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Concrete
Suitable for material	Stone
Suitable for material	Masonry
Type of product	Hammer drill

## Accessories

Carbide-tipped multi-purpose drill set long Drill Ø 6-12 mm	787055 6-12
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787000 5
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787000 8
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787000 4
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787000 10
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 12 mm	787060 12
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787000 12
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787000 6
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 6 mm	787060 6
Carbide-tipped multi-purpose drill Drill Ø 3 mm	787000 3
Carbide-tipped multi-purpose drill set Number of drills 7	787010 7
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 8 mm	787060 8
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 resistant to chemicals Rechargeable battery type, battery voltage MB18 V	073816 MB18