



Straight die grinder, Type: 722319



Order data

Order number	077261 722319
GTIN	4014586879444
Item class	03F

Description

Version:

- **Exceptionally handy straight die grinder.**
- **Quiet running due to multiple spindle bearings.**
- **Powerful motor with high cutting power.**
- **Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.**
- **Suitable for grinding points and carbide milling cutters.**
- **Powerful straight grinder with long spindle neck.**

Supplied with:

Collet Ø 6 mm, 2 chuck wrenches 13 AF and 17 AF.

Note:

Straight die grinders are approved for use with burrs up to a Ø of 12 mm.

Technical description

Power consumption	750 W
Manufacturer's designation	GSZ8-280PEL
Cable length	4 m
Weight	1.8 kg
maximum vibration to EN	< 2.5 m/s ²

electronic speed pre-selection	yes
Speed range	8500 - 28000 min ⁻¹
maximum collet Ø	6 mm
Power supply	Mains operated
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	077268 6
-------------------------------------------	----------