



Cordless hammer drill without battery, charger or case, Manufacturer's designation: M18CHPX

Order data

Order number	075532 M18CHPX
GTIN	
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **SDS plus chuck.**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

Supplied with:

Zero-speed version – without battery, charger and case.

Note:

Suitable carbide hammer drills can be found under No. 787000ff.

Suitable spare batteries and chargers can be found under No. 073808ff. and No. 073840.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Schaft: SDS Plus

Manufacturer's designation: M18CHPX

Battery voltage: 18 V

Battery capacity: 9 A·h

Speed range: 0 - 1350 rpm

maximum twist drill size Ø in steel: 13 mm

maximum twist drill size Ø in wood: 30 mm

Technical description

Type of product