



Straight die grinder, Type: 722322



Order data

Order number	077261 722322
GTIN	4014586880501
Item class	03F

Description

Version:

- Quiet running due to multiple spindle bearings.
- Powerful motor with high cutting power.
- Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.
- 4 m H07 industrial cable.
- Suitable for grinding points and carbide milling cutters.
- Exceptionally powerful FEIN ErgoGrip straight grinder.
- Ergonomically shaped handle.
- Great insertion depth, long neck bearing: 173 mm.
- POWERtronik with speed stabilisation and overload protection.
- With a long spindle neck.

Supplied with:

Including collet \varnothing 8 mm, 2 chuck wrenches 13 AF and 17 AF.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Straight die grinders are approved for use with burrs up to a \varnothing of 12 mm.

Manufacturer's designation: GSZ11-320PERL

Power consumption: 1010 W

Speed range: 9500 - 32500 rpm

maximum collet \varnothing : 8 mm

Weight: 2.1 kg

maximum vibration to EN: $< 2.5 \text{ m/s}^2$

Technical description

Weight	2.1 kg
maximum vibration to EN	< 2.5 m/s ²
Power consumption	1010 W
electronic speed pre-selection	yes
Manufacturer's designation	GSZ11-320PERL
Speed range	9500 - 32500 rpm
maximum collet Ø	8 mm

Accessories

Collet for straight grinder Collet Ø 8 mm	077268 8
---	----------