



## Straight die grinder, Type: 722322



### Order data

Order number	077261 722322
GTIN	4014586880501
Item class	03F

### Description

#### Version:

- **Exceptionally handy straight die grinder.**
- **Quiet running due to multiple spindle bearings.**
- **Powerful motor with high cutting power.**
- **Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.**
- **Suitable for grinding points and carbide milling cutters.**

With FEIN **ErgoGrip** for non-fatiguing work thanks to ergonomically designed handle.

Universal straight die grinder for working where access is difficult. Handy, slim neck enables internal grinding.

Powerful, handy straight die grinder with **short spindle neck**. Also suitable for semi-stationary use.

- **Exceptionally powerful FEIN ErgoGrip straight grinder.**
- **Great insertion depth, long neck bearing: 173 mm.**
- **POWERtronik with speed stabilisation and overload protection.**
- **With a long spindle neck.**

#### Supplied with:

Including collet Ø 8 mm, 2 chuck wrenches 13 AF and 17 AF.

#### Note:

Straight die grinders are approved for use with burrs up to a Ø of 12 mm.

### Technical description

Weight	2.1 kg
--------	--------

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Power consumption	1010 W
Cable length	4 m
electronic speed pre-selection	yes
Manufacturer's designation	GSZ11-320PERL
Speed range	9500 - 32500 min <sup>-1</sup>
maximum collet Ø	8 mm
Power supply	Mains operated
Type of product	Straight die grinder

---

## Accessories

Collet for straight grinder Collet Ø 8 mm	077268 8
---	----------