

**Cordless circular saw, Type: M12CCS44****Order data**

Order number	078207 M12CCS44
GTIN	4002395262816
Item class	03L

Description**Version:**

FUEL™ powerful cordless circular saw with brushless POWERSTATE™ motor.

- **Compact ergonomic design with knob handle.**
- **Integral dust extraction port for connection to an extraction system.**
- **Deep cuts and mitre cuts up to 50°.**
- **Sturdy magnesium fixed guard, swing guard and base plate.**

Supplied with:

Supplied with charger, hexagon L-wrench, 18-tooth carbide saw blade, parallel stop, carrying case (HD box).

Note:

See from No. 073814 and No. 073839 for suitable spare batteries and starter kits. For a suitable circular saw blade see No. 078212 size 18.

Technical description

Saw blade Ø	140 mm
maximum speed	3600 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²
Battery voltage	12 V

maximum cutting depth 90°	44 mm
Saw blade bore Ø	20 mm
Weight	2.7 kg
Battery capacity	4 Ah
Manufacturer's designation	M12CCS44-402C
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Modular case (HD=Heavy Duty)
Version	Hand-held circular saw
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Li-ion system M12B4 Battery type MB12	073815 MB12
Carbide saw blade Type 18	078212 18