

Sheet steel toolbox "Robust", Type: 5/430



Order data

Order number	693465 5/430
GTIN	2050001021762
Item class	66K

Description

Version:

Lockable with padlock (No. 085830 ff). Upper parts attached with continuous hinge strip.

Especially strong construction, in part of **0.9 mm sheet steel**.

Colour:

Tool box paint finish blue, powder-coated all round.

Technical description

External dimension width	200 mm
External dimension height	200 mm
Weight	5.3 kg
Version	5-part
External dimension length	430 mm
Type of product	Tool transport system

Accessories

Combination padlock Body Ø 40 mm	085885 40
Precision cylinder lock individual keys Body Ø 40 mm	085855 40
Cylinder padlock standard quality individual keys Body Ø 50 mm	085860 50
Precision cylinder lock with high shackle shared keys Body Ø 40 mm	085876 40
Precision cylinder lock with high shackle individual keys Body Ø 40 mm	085875 40
ALUTITAN padlock individual keys Body Ø 50 mm	085868 50
Precision cylinder lock individual keys Body Ø 50 mm	085850 50
Precision cylinder lock shared keys Body Ø 50 mm	085870 50
Combination padlock Body Ø 50 mm	085831 50
Cylinder padlock set 4 pieces per set, shared keys Body Ø 40 mm	085865 40
Cylinder padlock with high shackle individual keys Body Ø 40 mm	085866 40
Combination padlock with high shackle Body Ø 50 mm	085832 50
Cylinder padlock individual keys Body Ø 50 mm	085890 50
Combination padlock Body Ø 40 mm	085830 40
Cylinder padlock with high shackle individual keys Body Ø 40 mm	085882 40
Cylinder padlock individual keys Body Ø 50 mm	085880 50