



LED cordless lamp 0 version without battery, 12 V, Type: M12TLED



Order data

Order number	073210 M12TLED
GTIN	4002395380213
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity. Hand-held lamps with adjustable LED lamp head.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Milwaukee 12 V batteries MB12.

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Manufacturer's designation	M12TLED-0
Battery voltage	12 V
IP Index of Protection	IP 54
Number of rechargeable batteries contained	0

Type of rechargeable battery	Lithium-ion
Illumination	120 lm
Power supply	Rechargeable battery-powered
Pivot range	0 - 90 degrees
Product name attribute	12 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of product	Work lamp

Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M12B4 Battery type MB12	073815 MB12
Battery charger Type M1218FC	073840 M1218FC