


3M Scotch-Brite™

Bristle-Brush type A Ø 150 mm, BB-ZB, Grit: 80**Order data**

Order number	573565 80
GTIN	480112760694
Item class	53M

Description**Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

With oblique bristles (type A) for **powerful performance.**

Application:

Ensure the correct direction of rotation.

On virtually all materials, with the highest possible safety. Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

Bore Ø 25.4 mm, with reducer rings Ø 22.23 / 19 / 15.6 / 12.7 mm supplied. Extendable to any width with adaptor No. 573580. For use on double grinding machines or on straight grinders on flexible shafts with mandrel No. 556380 size 1.

Technical description

Grit	80
Brush Ø D ₁	150 mm

Colour	yellow
Brush width	12 mm
maximum speed	6000 min ⁻¹
Grinding medium code	Ceramic
Product name attribute	BB-ZB
Manufacturer's designation	BB-ZB
Type of product	Wheel brush

Accessories

Mandrel Number of discs to be clamped 1-2	556380 1-2
Extension adapter set, 4 pieces	573580
Mandrel Number of discs to be clamped 1	556380 1