


Garant**Open storage bin set, anthracite, Type: AA1****Order data**

Order number	963308 AA1
GTIN	4045197725370
Item class	91F

Description**Version:**

Open storage bin with ergonomic handle (comfortable to carry). Can be converted to a storage box by fitting a transparent cover. Inner faces polished smooth, allowing easy removal of parts and easy cleaning. Facility to apply labels on labelling strips at the front, and also by inserting cards (credit card size 85.6 × 54 mm) at the back. Open storage bins are stackable.

Advantage:**GARANT open storage bins and their advantages:**

- **Sturdy and stable thanks to impact resistant polypropylene.**
- **High load capacity due to reinforced bases and side walls.**
- **Easily stacked using the registration points.**
- **Pleasant to handle and easy to clean due to high-quality surfaces and smooth inner faces.**
- **Wide variety of application options.**

Suitable for:

Storage bin racks No. 916535, Multifix 923205, 962950, for rack panels No. 957060 size S in modular cabinets and for shelving cabinets / wall cabinets No. 954600 - 954670 and No. 954701 to 954722. In addition, the bin support No. 963137 allows small open storage bins No. 963301 size AA1 and AB1 to be hung individually on perforated panels.

Note:

Easyfix universal box holders No. 955810 size 100 are required for attaching to perforated panels. Suitable for sizes AA1, AB1 and AC1.

Only sizes AA1, AB1 and AC1 are suitable for direct mounting on multifix rails.

Technical description

Contents per box	48
Depth	103 mm
Height	65 mm
Material	Polypropylene
stackable	yes
Width	130 mm
Type	AA1
Facility to apply labels	by means of labelling strips
prepared for viewing window as loose goods divider	yes
prepared for viewing window	yes
Colour	anthracite
Stop in drawers	no
prepared for EAN code on the rear	yes
Product name attribute	anthracite
Colour	anthracite
Type of product	Open storage bins

Accessories

Open storage bin Type AA1	963301 AA1
---------------------------	------------