

**Grip wrench PLUS with adjustable lower jaw, overall length: 250mm****Order data**

Order number	708901 250
GTIN	3662424019838
Item class	73R

**Description****Version:**

Easy and safe to use. Trouble-free and quick opening by the **release lever** on the lower handle. With large clamping range and clamping depth, 5-step quick adjustment and additional fine adjustment. Lower jaw deeply cranked for clamping U-shaped and angle profiles, pipes etc. Serrated gripping jaws and special stable spring steel body. Fully nickel-plated.

**Application:**

For secure gripping of profiled, flat, and tubular materials. Clamping force adjustable up to 10,000 N.

**Material:**

Chrome molybdenum vanadium steel jaws; drop forged.

**Technical description**

overall length	250 mm
Jaw length	60 mm
Jaw capacity angled materials	50 mm
Jaw capacity round materials	110 mm
Type of product	Grip wrench