

AEG

Sabre saw, Type: US1300XE



Order data

Order number	078225 US1300XE
GTIN	4002395197675
Item class	07A

Description

Version:

Powerful 1300 W **AEG sabre saw**, ideal for cutting wood, plastic, metal pipes and profiles.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Transport case, saw blade.

Note:

Sabre saw blades can be found from No. 588600.

Packaging: Carrying case

Manufacturer's designation: US1300XE

Power consumption: 1300 W

Stroke length: 30 mm

Rate of strokes: 0 - 2800 min⁻¹

Weight: 3.8 kg

maximum vibration to EN: 18.5 m/s²

Technical description

maximum vibration to EN	18.5 m/s ²
Manufacturer's designation	US1300XE
Special features	FIXTEC
Rate of strokes	0 - 2800 min ⁻¹

Power consumption	1300 W
Stroke length	30 mm
Weight	3.8 kg
Packaging	Carrying case
Power supply	Mains operated
Type of product	Saw

Accessories

Sabre saw blades set Designation 1122EF	588600 1122EF
Sabre saw blades set Designation 922EF	588600 922EF
Sabre saw blades set Designation 1155CHM	588600 1155CHM
Sabre saw blades set Designation 922BF	588600 922BF
Sabre saw blades set Designation 1122BF	588600 1122BF
Sabre saw blades set Designation 922EHM	588600 922EHM