

**Garant**

**Workstation with electric height adjustment Load capacity max. 350 / 300 kg  
dark Eluplan worktop, Type: 1500/S**

**Order data**

Order number	920306 1500/S
GTIN	4062406120788
Item class	9GG

**Description****Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **with** side plates, suitable for installing in a row.

**Colour:**

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

**Recommendation:**

Light assembly work, sitting and standing.

**Note:**

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

**Technical description**

Weight	89 kg
Worktop thickness	50 mm
maximum load capacity	350 kg
Depth	750 mm
Width	1500 mm

Continuous load capacity	350 kg
Material of worktop	Eluplan, dark
Worktop depth	750 mm
Height adjustment range (worktop surface) from – to	720 - 1200 mm
Control panel with display and memory functions	yes
Worktop length	1500 mm
Lifting speed	22 mm/s
Workbench/desk load capacity - maximum distributed load (on wood)	350 kg
Plug type, input	F
Nominal voltage	250 V
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table