


**Garant****Burr Z FINE – very fine, Carbide, Type: G0618****Order data**

Order number	540440 G0618
GTIN	4045197725783
Item class	51D

**Description****Version:**Shank  $\varnothing$  6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Toothing grit designation	very fine
Tooth type abbreviation	Z FINE
Shape description	Pointed arch
Shape	G0618
Head $\varnothing$	6 mm
Overall length	50 mm
Shank $\varnothing$	6 mm
Head length	18 mm

Series	Tooth configuration Z FINE
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		