

Garant**Vernier caliper, Measuring range: 300mm****Order data**

Order number	410100 300
GTIN	4062406122157
Item class	40Z

Description**Version:**

Satin chromium plated anti-glare scales.
Fine, high-contrast scale.
Locking screw at the top.
Ergonomically optimised caliper.
Precision lapped measuring faces. Without depth gauge.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Graduation	1/128 in
Graduation	1/20 mm
Packaging	Wallet
Scale divisions	0.05 mm
Measuring range	0 - 300 mm
Reversible reading	mm / inch
Standard	ISO 13385
Jaw length	64 mm
Calibration	A1
Measurement deviation E MPE	± 0.05 mm

Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300