

**Garant****Vernier caliper Vernier 1/50, Measuring range: 200mm****Order data**

Order number	410105 200
GTIN	4062406122164
Item class	40Z

**Description****Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Better reading due to a colour-contrast scale.

Precision lapped measuring faces.

**Optional extras:**

Thread table No. 412180 for caliper back.

**Technical description**

Graduation	1/50 mm
Calibration	A1
Packaging	Wallet
Scale divisions	0.02 mm
Measuring range	0 - 200 mm
Reversible reading	mm / inch
Jaw length	50 mm
Graduation	1/128 in
Standard	ISO 13385
Depth gauge	Ø 1.6

Depth gauge available	yes
Measurement deviation E MPE	±0.03 mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200